


RCT™ Series Product Comparison



Model	No. of Lamps	Lumen Output	Types of Lamps Operated	Ballast Dimensions (L x W x H)	Features
B30RCT	1 or 2 lamps	1800 - 3500 lm	One 17 - 215 W (2' - 8') or two 17 - 40 W (2' - 4') T8, T9, T10 or T12 lamps; one 18 - 55 W or two 18 - 39 W (4-pin) long compacts; one 16 - 55 W or two 16 - 38 W (4-pin) 2D lamps	16.3" x 5.5" x 1.7" (414 mm x 138 mm x 44 mm)	Provides 30-second and 90-minute remote control testing; Works with WHRCT remote control transmitter (sold separately); Includes 2' flexible conduit; UL Listed / CSA Certified
B50RCT	1 or 2 lamps	900 to 1400 lm	One 17 - 215 W (2' - 8') or two 17-40 W (2' - 4') T8, T9, T10 or T12 lamps or one 18 - 55 W or two 18 - 39 W (4-pin) long compacts.	13.3" x 2.4" x 1.5" (339 mm x 60 mm x 38 mm)	Provides 30-second and 90-minute remote control testing; Works with WHRCT remote control transmitter (sold separately); Includes 2' flexible conduit; UL Listed



Model	Application	Emergency Ballast Compatibility	Ballast Dimensions (L x W x H)	Features
RCT-A Module	Converts existing fluorescent fixtures and select Philips Bodine emergency ballasts into remote control testing emergency lighting.	B33, B30, B50, B50U, BDL500, B60, BDL600, B84C, B426, BDL426, LP550, LP600, GEN1 & GEN3	8" x 1.2" x 1.15" (204 mm x 30.5 mm x 29.2 mm)	Enables 30-second and 90-minute remote control testing; Works with WHRCT remote control transmitter (sold separately); UL Listed
RCT-C Module	Converts existing fluorescent fixtures and select Philips Bodine emergency ballasts into remote control testing emergency lighting.	B33, B30, B50, B50U, BDL500, B60, BDL600, B84C, B426, BDL426, LP550, LP600, GEN1 & GEN3	8" x 1.2" x 1.15" (204 mm x 30.5 mm x 29.2 mm)	Enables 30-second and 90-minute remote control testing; Works with WHRCT remote control transmitter (sold separately); Includes 2' flexible conduit; UL Listed